

SHS-100

Cradle makes call button easy to move and remove from the patient bed

A magnet is embedded into the inside of call button for easy attachment to the patient bed

A hand-held nurse call button-perfect size for grip

2 Type of nurse call button-specially designed for hospital

Nurse can take care of their patients immediately

Description


Easy removal with cradle

Magnet embedded

Ergonomic design

Features

- Take care of patients promptly
- Suitable solution for urgent situation
- Decrease response time
- Cost-effective wireless solution
- Improve work efficiency





available in
2 colors



Cradle included

Size Info



SHS-100
2 Type of Nurse Call Button
( Call the nurse /  Clear the call)

PRODUCT SPECIFICATION

Specification

Number of buttons	2
Dimension	W37 x L99 x H10mm
Net Weight	148g
Color	Blue/Gold
Frequency Range	FM 433MHz
Power Source	DC 3V coin battery (CR2023)
Battery Life	Approx. calling 40,000 times
Antenna Type	Helical Antenna
Compatibility	with all Syscall receivers and the repeater

SYSTEM MAP

- The call bell number will be displayed on the receiver with a sound.



- The direct pager can receive call directly from the transmitters.



- The emergency light indicator can receive the call directly from the transmitter.

